


HIGH VOLTAGE:
 CAPACITOR START CAPACITOR RUN
 NO OVERLOAD SELECT ROTATION
 REMOTE MOUNTED RUN & START CAPACITOR.

RUN CAPACITOR SILVER METAL CANISTER
 START CAPACITOR BLACK PLASTIC PHENOLIC.


HIGH VOLTAGE. C.C.W.



HIGH VOLT. C.C.W. ROT.

BLUE (T1) — L1
 RED (T8) — L2
 YELLOW (T5) — L2
 WHITE (T4) — L2

FOR C.W. ROTATION
 INTERCHANGE
 RED (T8) AND
 YELLOW (T5)

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN PST 9/02/2013
				DEC.	INCHES		CHK SK 09/02/2013
				.X	±.1		APPD
				.XX	±.02		SCALE 1:1
				.XXX	±.005		REF 102006-150LE
01		DWH		.XXXX	±.0005	MAT'L.	FMF
NO.	REVISION	BY & DATE	CHK	ANG	±'7'30"	FINISH	PREV EXSPR112637
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE 102006-157LE	SIZE A
				DIST LB			DRAWING NO. PAGE 1 OF 1 102006-157LE
							REV.