



MAXIMUM FACE RUNOUT TO BE .004 T.I.R.  
 MAXIMUM PILOT ECCENTRICITY .004 T.I.R.  
 PERMISSIBLE SHAFT RUNOUT .002 T.I.R.

GASKETS THROUGHOUT

				TOLERANCES UNLESS SPECIFIED		<b>LEESON</b>	ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN MGM 04/09/03		
				DEC.	INCHES			CHK RDW 04/09/03	APPD	
				.X	$\pm$ .1			SCALE 3=8		
				.XX	$\pm$ .03	TITLE	OUTLINE - 56HC FRAME TEFC - RIGID "C"	REF		
02	UPDATED SHAFT EXT DIMS	RDW 4/26/04	SW	.XXX	$\pm$ .005			FMF		
01	CONDUIT HOLE WAS 1/2-14 NPT, DIM .157 WAS .12	SW 10/7/2003	RDW	.XXXX	$\pm$ .0005	MAT'L.		PREV		
NO.	REVISION	BY & DATE	CHK	ANG	$\pm$ 1/2'	FINISH				
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP		CAD FILE	16992800	SIZE	DRAWING NO.	REV.
				DIST				A	169928.00	01